

Garant
Combination spanner set, long version, Number of keys: 9

Order data

Order number	614610 9
GTIN	4062406219697
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. **Ring end deep cranked.**

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Supplied with:

1 each combination spanner No. 614600 / 614200 / 614900: Size 10; 13; 16; 17; 18; 19; 21; 22; 24

Note:

HT-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **HT-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

Width across flats	metric
Number of keys	9
Ring setting	10 degrees
Material	Chrome vanadium steel

Surface	matt chrome-plated
Ring end deep cranked	yes
Long version	yes
Type of product	Spanner

Accessories

Combination spanner, long version Width across flats 17 mm	614600 17
Combination spanner, long version Width across flats 22 mm	614600 22
Combination spanner, long version Width across flats 13 mm	614600 13
Combination spanner, long version Width across flats 19 mm	614600 19
Combination spanner, long version Width across flats 21 mm	614600 21
Combination spanner, long version Width across flats 18 mm	614600 18
Combination spanner, long version Width across flats 10 mm	614600 10
Combination spanner, long version Width across flats 16 mm	614600 16
Combination spanner, long version Width across flats 24 mm	614600 24