

Garant
Combination spanner, Width across flats: 14mm

Order data

| | |
|--------------|---------------|
| Order number | 613600 14 |
| GTIN | 4062406220068 |
| Item class | 61A |

Description
Version:

Drop-forged. With close tolerance jaw width.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance. Ring end with **HT-Drive** profile.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Note:

HT-Drive – the particularly close-fitting profile.

Advantage:

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

| | |
|---------------------------------|------------|
| Width across flats | 14 mm |
| maximum ring height $h_{2\max}$ | 12 mm |
| Spanner length L | 165 mm |
| Width across flats | metric |
| maximum jaw height h_1 | 6.5 mm |
| Standard | DIN 3113 A |

| | |
|-----------------------|-----------------------|
| Standard | ISO 3318 |
| Standard | ISO 7738 |
| Manufacturing process | drop forged |
| Material | Chrome vanadium steel |
| Surface | matt chrome-plated |
| Type of product | Spanner |