

Garant**Double open ended spanner, Jaw widths: 14X15mm****Order data**

Order number	610600 14X15
GTIN	4062406220273
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, non-flaking, matt chrome-plated.

Technical description

maximum jaw width b1	33 mm
Width across flats 1	14 mm
Width across flats 2	15 mm
maximum jaw height h	6 mm
maximum jaw width b2	35 mm
Spanner length L	190 mm
Width across flats	metric
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees

Jaw position 2	15 degrees
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner