

**Garant**
**Double-ended ring spanner, deeply cranked, Width across flats: 16X18mm**

**Order data**

Order number	615600 16X18
GTIN	4062406220952
Item class	61A

**Description**
**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

**Standard:**

**DIN 838 / ISO 3318**

**Material:**

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

**Note:**

**HT-Drive** – the particularly close-fitting profile.

**Advantage**

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

**Technical description**

maximum ring $\varnothing D_1$ max	25 mm
maximum ring $\varnothing D_2$ max	27 mm
Width across flats	metric
Width across flats 2	18 mm
Width across flats 1	16 mm

Spanner length L	270 mm
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Ring end deep cranked	yes
open ring	no
Type of product	Spanner