

Garant**Double open ended spanner, Jaw widths: 10X13mm****Order data**

| | |
|--------------|---------------|
| Order number | 610600 10X13 |
| GTIN | 4062406220211 |
| Item class | 61A |

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, non-flaking, matt chrome-plated.

Technical description

| | |
|----------------------|------------|
| Spanner length L | 170 mm |
| maximum jaw height h | 6 mm |
| Width across flats 2 | 13 mm |
| Width across flats 1 | 10 mm |
| Width across flats | metric |
| maximum jaw width b2 | 31 mm |
| maximum jaw width b1 | 26 mm |
| Standard | DIN 3110 |
| Standard | ISO 3318 |
| Jaw position 1 | 15 degrees |

| | |
|---|-----------------------|
| Jaw position 2 | 15 degrees |
| Material | Chrome vanadium steel |
| Surface | matt chrome-plated |
| non-sparking | no |
| both sides have the same width across flats | no |
| Type of product | Spanner |