

**Garant**
**Double open ended spanner, Jaw widths: 12X13mm**

**Order data**

Order number	610600 12X13
GTIN	4062406220228
Item class	61A

**Description**
**Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, non-flaking, matt chrome-plated.

**Technical description**

maximum jaw width b2	31 mm
Width across flats 1	12 mm
Width across flats	metric
maximum jaw width b1	29 mm
maximum jaw height h	6 mm
Width across flats 2	13 mm
Spanner length L	170 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees

Jaw position 2	15 degrees
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner