

**Garant**
**Combination spanner, long version, Width across flats: 27mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 614600 27     |
| GTIN         | 4062406220754 |
| Item class   | 61A           |

**Description**
**Version:**

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. **Ring end deep cranked.**

**Standard:**

**DIN 3113 B / ISO 3318 / ISO 7738**

**Material:**

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

**Note:**

**HT-Drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **HT-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

**Technical description**

|                                       |             |
|---------------------------------------|-------------|
| maximum jaw height h1                 | 12 mm       |
| maximum ring height h <sub>2max</sub> | 18 mm       |
| Width across flats                    | metric      |
| Width across flats                    | 27 mm       |
| Spanner length L                      | 385 mm      |
| Ring setting                          | 10 degrees  |
| Manufacturing process                 | drop forged |

|                       |                             |
|-----------------------|-----------------------------|
| Material              | Chrome alloy steel          |
| Surface               | chromium-plated over nickel |
| non-sparking          | no                          |
| Ring end deep cranked | yes                         |
| Type of product       | Spanner                     |