

**Garant****Double open ended spanner, Jaw widths: 24X26mm****Order data**

Order number	610600 24X26
GTIN	4062406220402
Item class	61A

**Description****Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, non-flaking, matt chrome-plated.

**Technical description**

Spanner length L	270 mm
maximum jaw width b1	54 mm
Width across flats 2	26 mm
Width across flats 1	24 mm
Width across flats	metric
maximum jaw width b2	58 mm
maximum jaw height h	9 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees

Jaw position 2	15 degrees
Material	Chrome vanadium steel
Surface	matt chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner