

Garant**Combination spanner, long version, Width across flats: 14mm****Order data**

Order number	614600 14
GTIN	4062406220655
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw width.

With easy-grip profile shaft. Exceptional tool life and wear resistance. **Ring end deep cranked.**

Standard:

DIN 3113 B / ISO 3318 / ISO 7738

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Note:

HT-Drive – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **HT-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

Width across flats	14 mm
Width across flats	metric
Spanner length L	210 mm
maximum ring height $h_{2\max}$	10 mm
maximum jaw height h_1	6.5 mm
Ring setting	10 degrees
Manufacturing process	drop forged

Material	Chrome alloy steel
Surface	chromium-plated over nickel
non-sparking	no
Ring end deep cranked	yes
Type of product	Spanner