

Garant**Double-ended ring spanner, deeply cranked, Width across flats: 36X41 mm****Order data**

Order number	615600 36X41
GTIN	4062406221102
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

Standard:

DIN 838 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Note:

HT-Drive – the particularly close-fitting profile.

Advantage

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Technical description

Width across flats 1	36 mm
maximum ring $\varnothing D_2$ max	60 mm
Width across flats	metric
Width across flats 2	41 mm
maximum ring $\varnothing D_1$ max	53 mm

Spanner length L	440 mm
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Ring end deep cranked	yes
open ring	no
Type of product	Spanner