

Garant
Combination spanner, Width across flats: 36mm

Order data

Order number	613600 36
GTIN	4062406220570
Item class	61A

Description
Version:

Drop-forged. With close tolerance jaw width.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance. Ring end with **HT-Drive** profile.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Note:

HT-Drive – the particularly close-fitting profile.

Advantage:

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

maximum jaw height h1	15 mm
Spanner length L	460 mm
Width across flats	36 mm
maximum ring height h _{2max}	24 mm
Width across flats	metric
Standard	DIN 3113 A

Standard	ISO 3318
Standard	ISO 7738
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner