

**Garant**
**Double-ended ring spanner, deeply cranked, Width across flats: 22X24mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 615600 22X24  |
| GTIN         | 4062406221034 |
| Item class   | 61A           |

**Description**
**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

**Standard:**

**DIN 838 / ISO 3318**

**Material:**

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

**Note:**

**HT-Drive** – the particularly close-fitting profile.

**Advantage**

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

**Technical description**

|                                    |        |
|------------------------------------|--------|
| Width across flats 1               | 22 mm  |
| Width across flats                 | metric |
| maximum ring $\varnothing D_2$ max | 37 mm  |
| Width across flats 2               | 24 mm  |
| Spanner length L                   | 330 mm |

|                                    |                       |
|------------------------------------|-----------------------|
| maximum ring $\varnothing D_1$ max | 34 mm                 |
| Ring setting                       | 75 degrees            |
| Manufacturing process              | drop forged           |
| Material                           | Chrome vanadium steel |
| Surface                            | matt chrome-plated    |
| Ring end deep cranked              | yes                   |
| open ring                          | no                    |
| Type of product                    | Spanner               |