

**Garant****Double open ended spanner, Jaw widths: 32X36mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 610600 32X36  |
| GTIN         | 4062406220464 |
| Item class   | 61A           |

**Description****Version:**

Drop-forged. With close tolerance jaw widths.

With optimised profile shank for specially secure grip and ergonomic working. Exceptional tool life and wear resistance.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, non-flaking, matt chrome-plated.

**Technical description**

|                      |            |
|----------------------|------------|
| Width across flats   | metric     |
| maximum jaw width b1 | 70 mm      |
| maximum jaw height h | 10 mm      |
| Spanner length L     | 325 mm     |
| maximum jaw width b2 | 80 mm      |
| Width across flats 2 | 36 mm      |
| Width across flats 1 | 32 mm      |
| Standard             | DIN 3110   |
| Standard             | ISO 3318   |
| Jaw position 1       | 15 degrees |

|   |                       |
|---|-----------------------|
| Jaw position 2                              | 15 degrees            |
| Material                                    | Chrome vanadium steel |
| Surface                                     | matt chrome-plated    |
| non-sparking                                | no                    |
| both sides have the same width across flats | no                    |
| Type of product                             | Spanner               |