

**Garant****Double-ended ring spanner set, deeply cranked, Number of keys: 10****Order data**

Order number	615610 10
GTIN	4062406221119
Item class	61A

**Description****Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

**Standard:**

**DIN 838 / ISO 3318**

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×24; 27×30

**Note:**

**HT-Drive** – the particularly close-fitting profile.

**Advantage**

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

**Technical description**

Width across flats	metric
Number of keys	10
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	matt chrome-plated
Measurement system metric	yes
Measurement system imperial	no
Ring end deep cranked	no
Type of product	Spanner

## Accessories

Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615600 16X17
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615600 6X7
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615600 12X13
Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615600 8X9
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615600 10X11
Double-ended ring spanner, deeply cranked Width across flats 21X24 mm	615600 21X24
Double-ended ring spanner, deeply cranked Width across flats 20X22 mm	615600 20X22
Double-ended ring spanner, deeply cranked Width across flats 27X30 mm	615600 27X30
Double-ended ring spanner, deeply cranked Width across flats 18X19 mm	615600 18X19
	615600 14X15

Double-ended ring spanner, deeply cranked Width across flats 14X15 mm

---