

Garant
Die, UNC: 2-4,5


Order data

Order number	142520 2-4,5
GTIN	4062406224226
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For UNC uniform coarse threads ASME – B1.1.

Tolerance class: 2A

Threads per inch: 4.5

Thread Ø: 50.8 mm

External Ø: 90 mm

Height: 36 mm

Technical description

Threads per inch	4.5
External Ø	90 mm
Thread Ø	50.8 mm
Height	36 mm

Thread size	2-4,5 UNC
Cutting direction	right-hand
Thread type	UNC
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		