

**Garant**
**Die 6g, M: M56**


## Order data

Order number	140300 M56
GTIN	4062406221645
Item class	11K

## Description

### Version:

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 5.5 mm

External Ø: 105 mm

Height: 36 mm

## Technical description

External Ø	105 mm
Height	36 mm
Tolerance class	DIN 13 6g
Pitch	5.5 mm
Thread size	M56

Thread type	M
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		