

Garant
Die HSS, MF: 14X0,5


Order data

| | |
|--------------|---------------|
| Order number | 141050 14X0,5 |
| GTIN | 4062406222109 |
| Item class | 11K |

Description

Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

1¾ turns lead chamfer.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.5 mm

External Ø: 38 mm

Height: 11 mm

Technical description

| | |
|-----------------|-----------|
| Pitch | 0.5 mm |
| Height | 11 mm |
| External Ø | 38 mm |
| Tolerance class | DIN 13 6g |
| Thread size | M14×0.5 |

| | |
|-------------------|------------|
| Thread type | MF |
| Flank angle | 60 ° |
| Tool material | HSS |
| Standard | EN 22568 |
| Cutting direction | right-hand |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |