

**Garant****Die HSS, MF: 64X4****Order data**

Order number	141050 64X4
GTIN	4062406223199
Item class	11K

**Description****Version:**Closed, pre-slit form, **with tapered lead chamfer on both sides.****1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 4 mm

External Ø: 105 mm

Height: 22 mm

**Technical description**

External Ø	105 mm
Height	22 mm
Pitch	4 mm
Tolerance class	DIN 13 6g
Thread size	M64x4

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		