

Garant**Die Hexagon, M: M11****Order data**

Order number	140920 M11
GTIN	4062406221881
Item class	11K

Description**Version:**

External hexagon for standard socket size. **Without** tapered spiral point. **1³/₄ turns lead chamfer.**

Note:

For re-cutting damaged threads or for cutting where access is difficult.

Tolerance class: DIN 13 6g

Pitch: 1.5 mm

Width across flats: 27 mm

Height: 11 mm

Technical description

Pitch	1.5 mm
Width across flats	27 mm
Height	11 mm
Thread size	M11
Cutting direction	right-hand

Thread type	M
Flank angle	60 °
Tool material	HSS
Standard	DIN 382
Tolerance class	DIN 13 6g
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Oil	suitable		
dry	suitable only under restricted conditions		