

Garant**Die HSS, MF: 56X4****Order data**

| | |
|--------------|---------------|
| Order number | 141050 56X4 |
| GTIN | 4062406223182 |
| Item class | 11K |

Description**Version:**

Closed, pre-slit form, with tapered lead chamfer on both sides.
1¾ turns lead chamfer.

Technical description

| | |
|-----------------|-----------|
| Height | 22 mm |
| External Ø | 105 mm |
| Pitch | 4 mm |
| Tolerance class | DIN 13 6g |
| Thread size | M56x4 |
| Thread type | MF |
| Flank angle | 60 ° |
| Tool material | HSS |

| | |
|-------------------|------------|
| Standard | EN 22568 |
| Cutting direction | right-hand |
| Type of product | Die |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|---|----------------------|-----------------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |