

Garant
Die HSS, MF: 3,5X0,25


Order data

Order number	141050 3,5X0,25
GTIN	4062406223038
Item class	11K

Description

Version:

 Closed, pre-slit form, **with tapered lead chamfer on both sides.**
1¾ turns lead chamfer.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.25 mm

External Ø: 20 mm

Height: 5 mm

Technical description

External Ø	20 mm
Height	5 mm
Pitch	0.25 mm
Tolerance class	DIN 13 6g
Thread size	M3.5×0.25

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		