

Garant
Die HSS, MF: 85X2

Order data

Order number	141050 85X2
GTIN	4062406222994
Item class	11K

Description
Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

1¾ turns lead chamfer.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 2 mm

External Ø: 130 mm

Height: 25 mm

Technical description

External Ø	130 mm
Tolerance class	DIN 13 6g
Pitch	2 mm
Height	25 mm
Thread size	M85×2

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		