

**Garant**
**Die HSS, MF: 4,5X0,35**


### Order data

Order number	141050 4,5X0,35
GTIN	4062406223052
Item class	11K

### Description

**Version:**

 Closed, pre-slit form, **with tapered lead chamfer on both sides.**
**1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.35 mm

External Ø: 20 mm

Height: 5 mm

### Technical description

Tolerance class	DIN 13 6g
Pitch	0.35 mm
Height	5 mm
External Ø	20 mm
Thread size	M4.5×0.35

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		