

Garant
Die HSS, MF: 16X0,5


Order data

Order number	141050 16X0,5
GTIN	4062406222154
Item class	11K

Description

Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

1¾ turns lead chamfer.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.5 mm

External Ø: 45 mm

Height: 14 mm

Technical description

Pitch	0.5 mm
External Ø	45 mm
Tolerance class	DIN 13 6g
Height	14 mm
Thread size	M16×0.5

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		