

Garant**Die HSS, MF: 11X0,5****Order data**

Order number	141050 11X0,5
--------------	---------------

GTIN	4062406222031
------	---------------

Item class	11K
------------	-----

Description**Version:**

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

1¾ turns lead chamfer.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.5 mm

External Ø: 30 mm

Height: 11 mm

Technical description

External Ø	30 mm
------------	-------

Height	11 mm
--------	-------

Pitch	0.5 mm
-------	--------

Tolerance class	DIN 13 6g
-----------------	-----------

Thread size	M11×0.5
-------------	---------

Thread type	MF
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		