

Garant**Die HSS, MF: 16X1,25****Order data**

| | |
|--------------|----------------|
| Order number | 141050 16X1,25 |
| GTIN | 4062406222178 |
| Item class | 11K |

Description**Version:**Closed, pre-slit form, **with tapered lead chamfer on both sides.****1 3/4 turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 1.25 mm

External Ø: 45 mm

Height: 14 mm

Technical description

| | |
|-----------------|-----------|
| External Ø | 45 mm |
| Pitch | 1.25 mm |
| Tolerance class | DIN 13 6g |
| Height | 14 mm |
| Thread size | M16×1.25 |

| | |
|-------------------|------------|
| Thread type | MF |
| Flank angle | 60 ° |
| Tool material | HSS |
| Standard | EN 22568 |
| Cutting direction | right-hand |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |