

Garant
Die HSS-E, MF: 14X1,25


Order data

| | |
|--------------|----------------|
| Order number | 141055 14X1,25 |
| GTIN | 4062406223625 |
| Item class | 11K |

Description

Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 1.25 mm

External Ø: 38 mm

Height: 11 mm

Technical description

| | |
|-----------------|-----------|
| Tolerance class | DIN 13 6g |
| Pitch | 1.25 mm |
| Height | 11 mm |
| External Ø | 38 mm |
| Thread size | M14x1.25 |

| | |
|-------------------|------------|
| Thread type | MF |
| Flank angle | 60 ° |
| Tool material | HSS E |
| Standard | EN 22568 |
| Cutting direction | right-hand |
| Type of product | Die |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1100 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | | |
| INOX < 900 N/mm ² | suitable | | |
| INOX > 900 N/mm ² | suitable only under restricted conditions | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |