

SWISS TOOLS

Lever-lock toolholder right-hand, PSC, Shank \varnothing / insert size: 50/08HPmm



Order data

Order number	320305 50/08HP
GTIN	2050002039742
Item class	36D

Description

Note:

Order the suitable **HP nozzle** No. 320001 separately. Spare parts No.320610 – 320626 can be found in the spare parts list.

PSC clamping stud on request.

Technical description

Minimum pre-drill \varnothing D ₁ min	63 mm
Overhang dimension A	60 mm
Insert size	08
Shank \varnothing	50 mm
suitable indexable insert	WN.. 0804..
Spare part	P04
Axis tip distance f	35 mm
Overall length	90 mm
Adapter	PSC
Application type	right-hand

Arbor standard	ISO 26623-1
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw No. 3 Type P01	320611 P01
Tube pin No. 7 Type P06	320618 P06
Tube pin No. 7 Type P04	320618 P04
High-pressure cooling nozzle (HP) Type 63	320001 63
Toggle lever No. 4 Type P06	320612 P06
Clamping screw No. 3 Type D07	320611 D07
Nozzle ring No. 5 Type D07	320613 D07
Clamping screw No. 3 Type P05	320611 P05
Toggle lever No. 4 Type P01	320612 P01
Toggle lever No. 4 Type P05	320612 P05
Tube pin No. 7 Type P02	320618 P02
Clamping screw No. 3 Type P02	320611 P02
Tube pin No. 7 Type P01	320618 P01
Toggle lever No. 4 Type P02	320612 P02
Intermediate spacer No. 1 Type P06	320610 P06
Intermediate spacer No. 1 Type P04	320610 P04
Intermediate spacer No. 1 Type P05	320610 P05
Clamp No. 6 Type D07	320614 D07
Clamping screw No. 3 Type P06	320611 P06
Intermediate spacer No. 1 Type P01	320610 P01
Toggle lever No. 4 Type P04	320612 P04
Intermediate spacer No. 1 Type P02	320610 P02
Tube pin No. 7 Type P05	320618 P05

