



## Snipe-nose combination pliers, chrome-plated VDE insulated, overall length: 145mm



### Order data

Order number	701655 145
GTIN	4003773079361
Item class	73F

### Description

#### Version:

Gripping faces with special three-point contour for secure gripping of flat parts. Fast cutting thanks to high ratio compound action. Milled slot in the gripping area enables small workpieces such as nails, pins and bolts to be held and pulled. Handy for working in inaccessible locations. Slim head profile with tapered jaws.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

#### Standard:

**DIN ISO 5746.**

#### Material:

Special tool steel.

### Technical description

overall length	145 mm
Cutting capacity hard wire up to $\varnothing$	2 mm
Cutting capability medium hard wire up to $\varnothing$	3 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	Multi-component covering
Material	Special tool steel

Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers