



Cordless impact wrench / impact driver, Type: GDS18VLIHT



Order data

Order number	074052 GDS18VLIHT
GTIN	3165140861915
Item class	03B

Description

Version:

Cordless impact wrench / impact driver

- **Reversible.**
 - **Battery charge display.**
- Powerful 18V impact screwdriver for the **most demanding** screw tightening in metal.
- **Extremely robust and tough thanks to all-metal gearbox and metal casing.**
 - **One of the lightest high-torque impact screwdrivers.**
 - **Longer battery life thanks to innovative Cool-Pack technology.**

Advantage:

Torque 650 Nm for demanding applications.

Supplied with:

Supplied with 2× Li-ion batteries, charger, L-BOXX

Note:

Suitable replacement batteries and chargers can be found under No. 073851–073866.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GDS 18V-Li HT

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 5 A·h

Battery voltage: 18 V
 maximum screw Ø (8.8 - 12.9): M20

Technical description

maximum vibration to EN	12.5 m/s ²
Weight	3 kg
Tool arbor drive profile	External square drive
maximum screw Ø (8.8 - 12.9)	M20
Tool arbor size	1/2 in
suitable battery - supplier / battery type / voltage	Bosch 18 V
Number of impacts	0 - 2100 min ⁻¹
Battery voltage	18 V
Packaging	Modular case (L-Boxx)
Battery capacity	5 A·h
Manufacturer's designation	GDS 18V-Li HT
typical application	Heavy Duty
maximum torque hard	650 N·m
maximum speed 1st speed	1900 min ⁻¹
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type AL1860CV	073866 AL1860CV
Battery charger Type 1880CV	073866 1880CV

