



MultiTalent Cordless, Type: 71292561



Order data

Order number	077825 71292561
GTIN	4014586884141
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

MultiTalent – general-purpose oscillating tool for dismantling and renovating as an entry level into the professional class. Powerful high-performance motor designed for continuous use. Cordless device of the latest generation with the same performance as mains-powered devices.

Supplied with:

1 "cordless" tool case set containing charger, 1x abrasive plate, 3x each abrasive discs (80, 120, 180 grit), 1 E-Cut universal saw blade (29 mm).

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073834 ff and 073845 for suitable spare batteries and chargers.

suitable battery - supplier / battery type / voltage: Fein type E 12 V

Manufacturer's designation: AFMT 12 QSL

Battery capacity: 3 A·h
 Battery voltage: 12 V
 Toolholder: StarlockPlus, Starlock
 Speed of oscillation: 11000 - 18000 rpm
 Amplitude (oscillation movement): 2 × 1.6 degrees

Technical description

Battery voltage	12 V
Battery capacity	3 A·h
Manufacturer's designation	AFMT 12 QSL
Speed of oscillation	11000 - 18000 rpm
Weight	1.5 kg
Width across grinding plate head	80 mm
Amplitude (oscillation movement)	2 × 1.6 degrees
Toolholder	StarlockPlus, Starlock
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 12 V

Accessories

Battery charger Type FE30	073845 FE30
Battery charger Type FE50	073845 FE50
Li-ion battery Battery type, battery voltage FE12 V	073836 FE12