

**HSS core drill Depth of cut 25 mm, Ø DC: 14mm****Order data**

Order number	119010 14
GTIN	4014586611891
Item class	03G

Description**Version:**

HSS core drill with QuickIN arbor.

Overall length: 72 mm for all cutter sizes.

Suitable for:

Quick-change system saves time with key-less tool change.

Suitable for FEIN core drill units, with adaptor also for other makes. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.

Supplied with:

Without centring pin.

Note:

For FEIN core drill units see No. 076520/ 076524/ 076526 in section 0 – workshop accessories.
The centring pin No. 119019 is required when using the core drills 119010 and 119000.

Technical description

Nominal Ø D _c	14 mm
Tool material	HSS
Colour ring	without
Type of product	Hole saw

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		