



## HSS core drill Depth of cut 25 mm, Ø DC: 16mm



### Order data

Order number	119010 16
GTIN	4014586612263
Item class	03G

### Description

#### Version:

HSS core drill with QuickIN arbor.

**Overall length: 72 mm** for all cutter sizes.

#### Suitable for:

Quick-change system saves time with key-less tool change.

Suitable for FEIN core drill units, with adaptor also for other makes. The core drill cuts only a ring of material, saving approx. 40 % – 60 % cutting time.

#### Supplied with:

**Without** centring pin.

#### Note:

For FEIN core drill units see No. 076520/ 076524/ 076526 in section 0 – workshop accessories. The centring pin No. 119019 is required when using the core drills 119010 and 119000.

### Technical description

Nominal Ø D <sub>c</sub>	16 mm
Tool material	HSS
Colour ring	without
Type of product	Hole saw

### User data

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		