


**Garant**
**Grinding disc (CER), Ø 76.2 mm, Grit: 80**

**Order data**

Order number	553923 80
GTIN	4045197805362
Item class	51E

**Description**
**Version:**

Optimum connection between the backing pad and grinding disc by the quick-clamping system (internal thread). Easy and quick disc replacement by hand, even after heavy use.

Sanding disc is centralised, resulting in vibration-free concentricity.

**Ceramic grit (CER)** ideal for working on stainless steels and nickel alloys. High removal rate and cool cut.

**Application:**

**For efficient sanding down of small areas, even with varying contours** in tool, mould and model making, machine, plant and container building. Reduced tool changing times save costs on multi-stage operations.

**Note:**

Other dimensions and grits available on request.

**Technical description**

Grit	80
Disc Ø	76.2 mm
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Product name attribute	Ø 76.2 mm
maximum speed	20000 min <sup>-1</sup>
Type of product	Grinding wheel

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

## Accessories

Rubber backing pad shank Ø 6 mm medium hard External  
Ø 75M mm

553920 75M