



Safety helmet EuroGuard, Colour: WHITE



Order data

Order number	097816 WHITE
GTIN	4017765038038
Item class	09K

Description

Version:

Safety helmet of high-density polyethylene in modern design with **low weight** whilst at the same time offering optimised protective area. Highly suitable for use outdoors and at low temperatures down to -20°C. The front face offers a **printable area** 6 x 6 cm. The height adjustable internal fitments with six attachment points ensure high wearing comfort. Two side slots offer the option of attaching ear protection and face visor. With rain gutter, 30 mm Euroslot mountings, ecologically responsible synthetic leather sweatband and controllable side ventilation.

Application:

Building trade, building construction and civil engineering.

Standard:

DIN EN 397

Suitable for :

Shell-type ear defenders No. 097756; 097753

Spare part:

No. 097822 sweatbands in three different versions.

Material of helmet shell: HDPE

Weight: 340 g

Technical description

Weight	340 g
--------	-------

Colour	WHITE
Material of helmet shell	HDPE
Norm	DIN EN 397
Type of product	Safety helmet

Accessories

Ear defenders Peltor™ Optime™ helmet series Type 3	097753 3
Sweatband Type SL	097822 SL
Sweatband Type L	097822 L
Chinstrap Overhang 4P	097823 4P
Ear defenders Peltor™ X series helmet version Type X5	097756 X5
Ear defenders Peltor™ Optime™ helmet series Type 1	097753 1
Ear defenders Peltor™ X series helmet version Type X4	097756 X4
Ear defenders Peltor™ X series helmet version Type X2	097756 X2
Ear defenders Peltor™ X series helmet version Type X1	097756 X1
Sweatband Type HT	097822 HT
Ear defenders Peltor™ Optime™ helmet series Type 2	097753 2
Ear defenders Peltor™ X series helmet version Type X3	097756 X3