



Core drilling machine, Type: 727053



Order data

Order number	076520 727053
GTIN	4014586886039
Item class	03F

Description

Version:

- **High magnetic clamping force and safety circuit ensure safe working in any position.**
- **Integral coolant supply for clean cut and long tool life.**
- **Convenient magnetic clamping force display.**
- **Reversible (even for thread tapping).**
- **Weight-optimised design.**

Compact lightweight single-speed magnetic core drilling machine with high functionality and tilt sensor.

Supplied with:

Supplied with cooling lubricant tank, lashing strap, 1× centring pin, swarf hook, carrying case.

Optional extras:

On request.

Note:

See from No. 119000 for carbide core drills and arbors. Suitable QuickIN-Max arbor and carbide core drills max. DM 100 mm available on request.

Technical description

maximum machine tap Ø in steel	M14 mm
maximum core drill Ø in steel	12 - 35 mm
Height	603 mm
maximum twist drill size Ø in steel	16 mm
maximum countersink Ø	31 mm
Tool arbor shape	QuickIN
AC supply voltage	230 V
Width	198 mm
Power consumption	1100 W
Length of magnetic base	175 mm
Manufacturer's designation	KBU35Q
maximum reamer Ø	16 mm
Working stroke	135 mm
Width of the magnetic base	80 mm
Speed range 1st speed	130 - 520 min ⁻¹
Length	311 mm
Weight	10.6 kg
Power supply	Mains operated
Packaging	Carrying case
Type of product	Core drilling machine

Accessories

Carbide core drillDepth of cut 35 mm Ø DC 15 mm	119000 15
Carbide core drillDepth of cut 35 mm Ø DC 38 mm	119000 38
Carbide core drillDepth of cut 35 mm Ø DC 16 mm	119000 16
Carbide core drillDepth of cut 35 mm Ø DC 40 mm	119000 40
Carbide core drillDepth of cut 35 mm Ø DC 20 mm	119000 20
Carbide core drillDepth of cut 35 mm Ø DC 28 mm	119000 28

Carbide core drillDepth of cut 35 mm Ø DC 55 mm	119000 55
Carbide core drillDepth of cut 35 mm Ø DC 24 mm	119000 24
Carbide core drillDepth of cut 35 mm Ø DC 13 mm	119000 13
Carbide core drillDepth of cut 35 mm Ø DC 50 mm	119000 50
Carbide core drillDepth of cut 35 mm Ø DC 26 mm	119000 26
Carbide core drillDepth of cut 35 mm Ø DC 30 mm	119000 30
Carbide core drillDepth of cut 35 mm Ø DC 35 mm	119000 35
Carbide core drillDepth of cut 35 mm Ø DC 45 mm	119000 45
Carbide core drillDepth of cut 35 mm Ø DC 17 mm	119000 17
Carbide core drillDepth of cut 35 mm Ø DC 22 mm	119000 22
Carbide core drillDepth of cut 35 mm Ø DC 12 mm	119000 12
Carbide core drillDepth of cut 35 mm Ø DC 62 mm	119000 62
Carbide core drillDepth of cut 35 mm Ø DC 25 mm	119000 25
Carbide core drillDepth of cut 35 mm Ø DC 43 mm	119000 43
Carbide core drillDepth of cut 35 mm Ø DC 65 mm	119000 65
Carbide core drillDepth of cut 35 mm Ø DC 18 mm	119000 18
Carbide core drillDepth of cut 35 mm Ø DC 32 mm	119000 32
Carbide core drillDepth of cut 35 mm Ø DC 14 mm	119000 14
Carbide core drillDepth of cut 35 mm Ø DC 60 mm	119000 60
Carbide core drillDepth of cut 35 mm Ø DC 52 mm	119000 52
Carbide core drillDepth of cut 35 mm Ø DC 21 mm	119000 21
Carbide core drillDepth of cut 35 mm Ø DC 36 mm	119000 36