



Single-speed power drill, Type: 720552



Order data

Order number	075110 720552
GTIN	4014586882413
Item class	03F

Description

Version:

Fein hand-held power drill –

- Precision drill chuck with full metal body.
- Stepless electronic speed control for a gentle start to drilling.
- Metal gearbox casing for secure bearing seatings.
- Additional serrated handle for a secure grip.
- FEIN sensitive handle for non-fatiguing and safe working.
- Integral switch for ease of use.

Compact, high speed.

Advantage:

Stepless electronic speed control.

Supplied with:

1 quick-clamping drill chuck 0.5 – 10 mm **with clamping force protection.**

Technical description

Drill chuck adapter	1/2 inch – 20 UNF
Reversible	yes
Weight	1.7 kg
maximum vibration to EN	< 2.5 m/s ²

Power consumption	500 W
Chuck clamping range	0.5 - 10 mm
maximum twist drill size Ø in steel	6 mm
Manufacturer's designation	BOP-6
maximum twist drill size Ø in wood	20 mm
Speed range	0 - 4000 min ⁻¹
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill