



Single-speed power drill, Type: 720553



Order data

Order number	075110 720553
GTIN	4014586882468
Item class	03F

Description

Version:

Fein hand-held power drill –

- **Precision drill chuck with full metal body.**
- **Stepless electronic speed control for a gentle start to drilling.**
- **Metal gearbox casing for secure bearing seatings.**
- **Additional serrated handle for a secure grip.**
- **FEIN sensitive handle for non-fatiguing and safe working.**
- **Integral switch for ease of use.**

Versatile use for drilling, countersinking and tapping.

Advantage:

Including drill chuck with clamping force protection.

Supplied with:

1 quick-clamping drill chuck 1.5 – 13 mm **with clamping force protection.**

Manufacturer's designation: BOP-10

Power consumption: 500 W

Drill chuck adapter: 1/2 inch – 20 UNF

Chuck clamping range: 1.5 - 13 mm

Speed range: 0 - 1500 min⁻¹

maximum twist drill size Ø in steel: 10 mm

Technical description

Manufacturer's designation	BOP-10
Chuck clamping range	1.5 - 13 mm
Drill chuck adapter	1/2 inch – 20 UNF
maximum vibration to EN	< 2.5 m/s ²
maximum twist drill size Ø in steel	10 mm
Power consumption	500 W
maximum twist drill size Ø in wood	30 mm
Weight	1.8 kg
Reversible	yes
Speed range	0 - 1500 min ⁻¹
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill