

**Garant****Screw-on toolholder, left-hand, Shank / insert size: 12/11mm****Order data**

Order number	260907 12/11
GTIN	4045197805911
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	16 mm
suitable indexable insert	TC.. 1102..
Shank size	12 mm
Head length L <sub>1</sub>	19 mm
Overall length L	80 mm
Insert size	11 mm
ISO code toolholder	STGCR/L 1212F11
Pack of insert screws	269028 18
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 18	269028 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500