

Garant
Screw-on toolholder, left-hand, Shank / insert size: 16/11mm


Order data

Order number	260907 16/11
GTIN	4045197805928
Item class	21T

Technical description

Head length L_1	19 mm
Insert size	11 mm
Overall length L	100 mm
Shank size	16 mm
ISO code toolholder	STGCR/L 1616H11
Functional width L_4	20 mm
Pack of insert screws	269028 18
suitable indexable insert	TC.. 1102..
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 18	269028 18
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500