

**Jigsaw, Type: GST150BCE****Order data**

Order number	078200 GST150BCE
GTIN	3165140463560
Item class	03B

**Description****Version:**

Bosch jigsaw with Bosch SDS System for simple cutting blade change, no tools required. Jigsaw with **D-shape handle**.

- **High power reserves, even in hard and thick beams, thanks to powerful 780-watt motor with overload capability.**
- **Extremely robust and distortion-resistant base plate for the heaviest duties.**

**Supplied with:**

Including 1× saw blade, protective cover, slide shoe, extraction adapter, suction nozzle, transport case.

**Technical description**

Rate of strokes	500 - 3100 min <sup>-1</sup>
Power consumption	780 W
Manufacturer's designation	GST150BCE
Weight	2.7 kg
maximum vibration to EN	7.0 m/s <sup>2</sup>
maximum sawn thickness steel	10 mm

maximum sawn thickness wood	150 mm
tool change without tools	yes, SDS system
Special features	Robust
Orbital stroke	4-way
Mitre angle adjustment	yes
suitable jigsaw blades	588400 – 588551
Packaging	transport suitcase
Format	D-shape handle
Power supply	Mains operated
Type of product	Saw

## Accessories

Jigsaw blades set Designation T118AHM	588400 T118AHM
Jigsaw blades set Designation T118A	588400 T118A
Jigsaw blades set Designation T318A	588400 T318A
Jigsaw blades set Designation T118AF	588400 T118AF
Jigsaw blades set Designation T127D	588400 T127D
Jigsaw blades set Designation T318B	588400 T318B
Jigsaw blades set Designation T118B	588400 T118B