

**Jigsaw, Type: GST160CE****Order data**

| | |
|--------------|-----------------|
| Order number | 078200 GST160CE |
| GTIN | 3165140746250 |
| Item class | 03B |

Description**Version:**

Bosch jigsaw with Bosch SDS System for simple cutting blade change, no tools required. Jigsaw with **straight handle**.

- **Highly precise saw blade guidance thanks to patented double roller which minimises saw blade bending – for outstanding precision of cutting.**
- **Powerful 800 Watt motor with constant speed electronics, with power in reserve even when cutting hard materials.**
- **Very low vibration, thanks to mass balancing system, for first-class smoothness in use.**

Supplied with:

Including 3 × saw blade, extraction adapter, L-BOXX 136, 1/1 L-BOXX inlay.

Technical description

| | |
|-----------------------------|------------------------------|
| Rate of strokes | 800 - 3000 min ⁻¹ |
| maximum sawn thickness wood | 160 mm |
| maximum vibration to EN | 7.5 m/s ² |
| Manufacturer's designation | GST160CE |
| Power consumption | 800 W |

| | |
|------------------------------|-----------------------|
| maximum sawn thickness steel | 10 mm |
| Mitre angle adjustment | yes |
| tool change without tools | yes, SDS system |
| suitable jigsaw blades | 588400 – 588551 |
| Weight | 2.2 kg |
| Orbital stroke | 4-way |
| Special features | High-power, LED |
| Packaging | Modular case (L-Boxx) |
| Format | Straight handle |
| Power supply | Mains operated |
| Type of product | Saw |

Accessories

| | |
|---------------------------------------|----------------|
| Jigsaw blades set Designation T318A | 588400 T318A |
| Jigsaw blades set Designation T127D | 588400 T127D |
| Jigsaw blades set Designation T118B | 588400 T118B |
| Jigsaw blades set Designation T118AHM | 588400 T118AHM |
| Jigsaw blades set Designation T118AF | 588400 T118AF |
| Jigsaw blades set Designation T318B | 588400 T318B |
| Jigsaw blades set Designation T118A | 588400 T118A |