

Garant**Cleaning propeller, Blade Ø: 260mm****Order data**

Order number	358950 260
GTIN	4062406229412
Item class	31E

Description**Version:**

- **Robust design.**
- **Opening and closing the vane by the speed of the spindle.**
- **Marked ends to the vanes, for optimum visibility.**
- **For installation in any toolholder with through-coolant capability.**

The machine must be started at 2000 rpm and slowly increased to 5000 rpm – 8000 rpm.

Advantage:

- **Efficient cleaning of clamping equipment, workpieces and work tables.**
- **Removal of accumulated chips and blowing out pockets of water.**
- **Perfect complement to the automated work process.**

Optional extras:

Spare cleaning propeller No. 358951 1 and 4.

Technical description

Shank Ø	20 mm
Speed range	5000 - 8000 min ⁻¹

Type of product	Cleaning propeller
-----------------	--------------------

Accessories

Spare cleaning propeller Type 1	358951 1
Spare cleaning propeller Type 4	358951 4
Spare spring set 4 pcs 4	358953 4