

Garant**Four-way ratchet ring spanner "4 in 1", Type: 21-27****Order data**

Order number	614847 21-27
GTIN	4062406229917
Item class	61B

Description**Version:**

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

maximum ring height h_2	30 mm
maximum ring \varnothing D1	40 mm
maximum ring height h_1	26 mm
Width across flats 4	27 mm
Width across flats 1	21 mm
Width across flats	metric
Width across flats 3	24 mm
Width across flats 2	22 mm
overall length L	275 mm
maximum ring \varnothing D2	52 mm
No. of teeth	72
Working arc	5 degrees

Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner