

Garant
Four-way ratchet ring spanner "4 in 1", Type: 12-15

Order data

Order number	614847 12-15
GTIN	4062406229900
Item class	61B

Description
Version:

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

maximum ring \varnothing D1	26.5 mm
Width across flats 1	12 mm
maximum ring height h_1	17.1 mm
maximum ring \varnothing D2	29.5 mm
Width across flats	metric
maximum ring height h_2	18 mm
Width across flats 4	15 mm
overall length L	190 mm
Width across flats 2	13 mm
Width across flats 3	14 mm
No. of teeth	72
Working arc	5 degrees

Material	Chrome vanadium steel
Surface	matt chrome-plated
Ratchet reversible	yes
Type of product	Spanner