



Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø h7: 8,4 mm

Order data

Order number	122505 8,4
GTIN	4045197391896
Item class	11E

Technical description

Through-coolant	yes, with 25 bar
Machining strategy	HPC
Pilot drill required	
Point angle	140 degrees
Helix angle	degrees
Coating	TiAlN
Hole tolerance	
Drill depth up to	4×D
Type	
Colour ring	green
Tool material	Solid carbide
Cutting direction	
Use for drilling	
Skaft	DIN 6535 HB to h6
Series	
Type of product	

