



Precision cylinder lock with high shackle shared keys, Body Ø: 40mm



Order data

Order number	085876 40
GTIN	4003482453124
Item class	08Q

Description

Version:

Solid brass body, rust-free precision lock mechanism, steel shackle hardened and chrome-plated, double locked.

With extra high shackle.

The 116 Profi range is available on request in the following special versions: Locks according to a sample pattern or locking, with master key system and additional keys.

The padlock has a solid brass body and is suitable for locking doors, objects and much more - it is even more flexible!

The special feature of this padlock is the unusually high shackle. This enables greater flexibility of use of the padlock in a wide variety of places. In addition the shackle of the lock is of hardened steel and is double locked. The internal mechanism of the 116 HM Profi has a precision mechanism optimally protected against rust by the brass casing.

Function:

Common key means the key can open and close **multiple** locks and cylinders.

Supplied with:

Padlock with 2 keys.

Technical description

Number of keys	2
Number of locks	1
Locking	shared keys
Shackle, double lever mechanism	yes
with keyhole cover	no
Material of the housing	Brass
Body Ø	40 mm
Internal height of shackle	60 mm
Series	116 Profi
tall shackle	yes
Hoop hardened	yes
Type of product	Padlock