

PRYOR

Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 5mm



Order data

Order number	085430 5
GTIN	5022044002951
Item class	08W

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Normal script; i. e. the punched character can be read directly on the component.

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

Shank thickness	9.5
Character height	5 mm

overall length	70 mm
Type of product	Hand punch

Accessories

Letter punch – individual height / Characters 5/L mm	085431 5/L
Letter punch – individual height / Characters 5/X mm	085431 5/X
Letter punch – individual height / Characters 5/K mm	085431 5/K
Letter punch – individual height / Characters 5/T mm	085431 5/T
Letter punch – individual height / Characters 5/E mm	085431 5/E
Letter punch – individual height / Characters 5/G mm	085431 5/G
Letter punch – individual height / Characters 5/C mm	085431 5/C
Letter punch – individual height / Characters 5/R mm	085431 5/R
Letter punch – individual height / Characters 5/F mm	085431 5/F
Letter punch – individual height / Characters 5/N mm	085431 5/N
Letter punch – individual height / Characters 5/B mm	085431 5/B
Letter punch – individual height / Characters 5/J mm	085431 5/J
Letter punch – individual height / Characters 5/V mm	085431 5/V
Letter punch – individual height / Characters 5/H mm	085431 5/H

Letter punch – individualNormal script A – Z Character height / Characters 5/P mm	085431 5/P
Letter punch – individualNormal script A – Z Character height / Characters 5/U mm	085431 5/U
Letter punch – individualNormal script A – Z Character height / Characters 5/O mm	085431 5/O
Letter punch – individualNormal script A – Z Character height / Characters 5/Q mm	085431 5/Q
Letter punch – individualNormal script A – Z Character height / Characters 5/I mm	085431 5/I
Letter punch – individualNormal script A – Z Character height / Characters 5/Y mm	085431 5/Y
Letter punch – individualNormal script A – Z Character height / Characters 5/W mm	085431 5/W
Letter punch – individualNormal script A – Z Character height / Characters 5/A mm	085431 5/A
Letter punch – individualNormal script A – Z Character height / Characters 5/D mm	085431 5/D
Letter punch – individualNormal script A – Z Character height / Characters 5/S mm	085431 5/S
Punch holder Type GRIP	085475 GRIP
Letter punch – individualNormal script A – Z Character height / Characters 5/& mm	085431 5/&
Letter punch – individualNormal script A – Z Character height / Characters 5/Z mm	085431 5/Z
Letter punch – individualNormal script A – Z Character height / Characters 5/M mm	085431 5/M