

Induction heater iDuctor Power W2300, Type: W2300KIT_B



Order data

Order number	078332 W2300KIT_B
GTIN	8718868455062
Item class	03S

Description

Version:

The iDuctor Power+ W2300 is a handy induction tool with a rated power of 2300 Watt. It allows large and heavy ferrous metal machine parts to be heated up and separated safely without exposure to naked flames. Flexcoils available in different lengths.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Technical description

Height	130 mm
Length	490 mm
Voltage	230 V
Width	390 mm
Output power	2300 W
Frequency range	50 - 60 Hz

IP Index of Protection	IP 20
Power supply	Mains operated
Weight	4 kg
Type of product	Induction heater