



Side lock arbor Form AD, BT 40 A = 100, Clamping range \varnothing D1: 10mm



Order data

Order number	302617 10
GTIN	4062406230340
Item class	32A

Description

Version:

All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	100 mm
External \varnothing D	35 mm
Spare clamping screw No. 30 9900	10
Clamping \varnothing D ₁	10 mm
Adapter	BT 40 A = 100
Standard	DIN 6359
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping Ø D1 10 mm	309900 10
----------------------------------------------------------	-----------